

Morgat

4391A2FK0







STANDARD
100
1012048
Centexbel



Jacket

The Morgat is the perfect jacket for people who work in the food industry. This jacket is easy to maintain and can be washed at 95 °C for optimum hygiene. In addition, the jacket is comfortable because of the light, elastic quality fabric. The underarm ventilation and the elastic wrist bands increase comfort.



SIOEN head office

Fabriekstraat 23
B-8850 Ardoorie

Belgium

T: +32 (51) 740 800

F: +32 (51) 740 962

www.sioen-ppc.com

© 2022 Sioen Apparel - Protection through Innovation, Flexothane®, Stoppo® and the SIOEN logo are trademarks of the Sioen Industries Group.
Please note that all information given in this document is intended to be useful and informative and is correct to the best of our knowledge at time of print.
No liability can be accepted for inaccuracies or omissions. The right is reserved to amend this information without prior notice.
All our technical files, style descriptions, presentations, designs and drawings, give the latest update of the standards and design or style features of each product. However, delivered products may comply with previous standards, design or style features. For that Sioen disclaims any liability whatsoever.
Contact our sales for full information if specific requirements are needed.



Discover
our products

Jacket

Morgat - 4391A2FKo

European Standards: (based upon size L)

- » EN 14605 : 2005 + A1 : 2009 Type PB (4)
- » EN 14126 : 2003 +AC : 2004 Type PB[4]-B
- » EN 343 : 2019 / Class 4-1-X
- » regulation 1935 : 2004
- » EN ISO 13688 : 2013 +A1 : 2021

Exterior:

- » Fixed hood
- » Zip closure under flap with press studs
- » Raglan sleeves
- » Elasticated wristband
- » Underarm ventilation
- » Back length 85 cm (L)

Fabric:

Flexothane® Kleen: 100% polyamide 6.6 knitting with PU coating; ± 170 g/m²

Sizes:

XXS - XXXL

Colour:

- » W02 White
- » H45 Royal Blue

Combining products:

6639

Packaging:

20 pieces per box

Wash and care instructions: